





5741 Buckingham Parkway, Unit B, Culver City, California 90230, USA Telephone: +1-310-822-1000, Facsimile: +1-310-338-3434

Email borin@borin.com - Web Site www.borin.com

<u>Date of Submittal</u>: Thursday, October 20, 2005 Revision Date: None

Technical Bulletin 0001

Subject: Soil Resistance Effects on Reference Electrodes

When the earth dries out around a stationary reference electrode the resistance to "remote earth" increases. This can affect the potential sensed by either a portable meter or a remote monitoring system. The sensed potential will decrease. The effect is minimized by using a high resistance meter circuit. The error can be calculated as follows:

True Potential = Measured Potential	X	Meter Resistance				
		Meter Resistance + Reference Resistance				

This assumes that the meter resistance and reference resistance are much higher than other resistance in the circuit, such as, lead wire resistance and the resistance of the buried structure to remote earth, which is almost always the case.

By the use of a reference electrode that has a large surface reading area (diafragma), from 210 to 360 square centimeters (33 to 50 square inches), combined with a mechanism to retain moisture in the reference cell the above effects are dramatically reduced but not eliminated, especially when the soil is very dry, (see drawing SRE-007-CUY).


The resistance of the reference electrode can be measured using a "Vibroground" or "Nilsson" type instrument or by the alternative method described and illustrated in page two of this technical bulletin titled "SRE Resistance to Remote Earth".

Manufacturing, Inc., General Offices: Los Angeles, Manufacturing Plants: Los Angeles, Germany, Latin America, Middle East,

Sales Offices & Distribution Centers: Abu Dhabi, Anchorage, Atlanta, Baltimore, Barcelona, Berlin, Billings, Bogotá, Bombay, Boston, Brussels, Budapest, Buenos Aires, Caracas, Ciudad de México, Chicago, Cleveland, Dammam, Denver, Detroit, Edmonton, Frankfurt, Guayaquil, Helsingborg, Houston, Hyderadad, Johannesburg, Karachi, Kuwait, London, Kuala Lumpur, Los Angeles, Manamah, Melbourne, Miami, Midland, Milan, Montreal, Moscow, New Orleans, New York, Oklahoma City, Oman, Paris, Pittsburgh, Prague, Reykjavik, Rio de Janeiro, Saint Louis, San Diego, San Francisco, Santiago, Seattle, Seoul, Singapore, Slovenia, Sioux Falls, Taipei, Tel Aviv, The Hague, Tokyo, Tulsa, Vienna, Warsaw, Wichita



Measurement of a Buried Stationary Reference Electrode Resistance to Remote Earth



The distance between the stationary reference electrode and the auxiliary ground rod should be 30 to 40 meters. The distance between the stationary reference electrode and the portable reference electrode should also be 30 to 40 meters. The distance between the auxiliary ground rod and the portable reference electrode should accordingly be 60 to 80 meters. The battery should have sufficient voltage to produce a current of at least 5 milliamps (50 Volts if the stationary reference electrode resistance is 100.000 ohms and less at lower reference electrode resistances). The soil around the driven auxiliary ground rod may be wetted to reduce overall circuit resistance.

The change in the potential difference between the portable and stationary reference electrodes, when the switch is closed, is measured.

The current flow with the switch closed is measured.

The resistance of the stationary reference electrode to remote earth is calculated as follows: R =

R = Resistance of stationary reference electrode to remote earth (ohms)

ΔV = Absolute value of the change in potential between portable and stationary reference electrodes when current is applied (Volts)


I = applied current (Amperes)

BORIN Manufacturing LLC

SRE Resistance to Remote Earth REVISION DRAWING NUMBER SIZE 1.0 Technical Bulletin TBE-0001 SCALE DATE February 29, 1992

2 of 2

Representative



"Stelth 2" Cu-CuSO4 Stationary Reference Electrode for underground or concrete service, chloride free conditions

#6 (16 mm2) to #24 (.25 mm2) and in all insulations standards.

Specifications: Copper-Copper Sulfate reference electrode		WARRANTY: 30 Year Design Life (-0 +2 years)			PODIN Manufacturing 110			
1. Medical grade ceramic body	6. Can be FROZEN !!!	PART NUMBER: SRE-007-CUY			BORIN Manufacturing LLC			
2. Element is 99.99% pure Copper	FINISHED GOODS:	SRE-007-CUY	DATE	"Stelth 2" Cu-CuSO4 reference cell				
3. 30 micron Ceramic Sensor	8. Hydrogen Sulfide Ion Trap	DESIGNED BY:	Frank W. Borin	2/29/1992	SIZE	REVISION	DRAWING NUMBER	
4. Stability 5 mV with 3 microA load	9. Chloride Ion Trap	DRAWN BY:	William H. Pruess	2/29/1992	A	A 1.1 SRE-007-CUY / TBE		TBE-0001
5. Temperature Range -10 to 176 degrees F, (-23 to 80 degrees C)		CHECKED BY:	Thomas Mierau	2/29/1992	1.0" = 1.0"		February 29, 1992	SHEET 3 of 3